Physikalisch-Technische Bundesanstalt



Braunschweig und Berlin

Member State of OIML Germany



OIML Certificate N° R60/2000-DE1-10.04

OIML CERTIFICATE OF CONFORMITY

Issuing Authority

Name: Address: Physikalisch-Technische Bundesanstalt Bundesallee 100, 38116 Braunschweig

Person responsible:

Dr. Dirk Ratschko

Applicant

Name:

Zhonghang Electronic Measuring Instruments Co., Ltd. (ZEMIC)

Address:

2 PO Box,

723007 Hanzhong, Shaanxi

China

Manufacturer of the certified type is the applicant.

Identification of the cer-

Strain gauge single point load cell

tified type

Type: B6N

Further characteristics see page 2

This Certificate attests the conformity of the above identified type (represented by the sample or samples identified in the associated Test Report) with the requirements of the following Recommendation of the International Organization of Legal Metrology (OIML):

R60, edition 2000 for accuracy class C3

This Certificate relates only to the metrological and technical characteristics of the type of instrument covered by the relevant OIML Recommendation identified above.

This Certificate does not bestow any form of legal international approval.

Physikalisch-Technische Bundesanstalt



OIML Certificate N° R60/2000-DE1-10.04

The conformity was established by the results of tests and examinations provided in the associated Test Report

No. 1.12 4044288-2

that includes 22 pages

The Issuing Authority

Dr. D. Ratschko Oberregierungsrat

27.04.2010

The CIML Member

Dr. R. Schwartz Direktor und Professor

27.04.2010

The load cells of the series B6N are single point load cells. They are made of stainless steel and the strain gauge application is hermetically sealed.

The metrological characteristics for application in approved weighing instruments are listed in table 1.

Table 1: Essential data

Accuracy class			C3
Maximum number of load cell intervals	n _{LC}		3000
Rated output		mV/V	2
Maximum capacity	E _{max}	kg	50 / 75 / 100 / 150 / 200
Minimum load cell verification interval	v _{min} = (E _{max} / Y)		E _{max} / 9000
Minimum dead load output return	DR = (½ E _{max} / Z)		½ E _{max} / 6000

Dead load: 0%·E_{max}; Safe overload: 150%·E_{max}; Input impedance: 430 Ω; Fraction: p_{LC} = 0.7

Important note: Apart from the mention of the Certificate's reference number and the name of the OIML Member State in which the Certificate is issued, partial quotation of the Certificate and of the associated Test Report is not permitted, although either may be reproduced in full.