

Sauter GmbH


Ziegelei 1 D-72336 Balingen E-Mail: info@kern-sohn.com Tel.: +49-[0]7433- 9933-0 Fax: +49-[0]7433-9933-149 Internet: www.sauter.eu

Datasheet / Manual

SAUTER CP P7

V. 1.1 06/2023 GB







SAUTER CP P7

V. 1.1 06/2023

Datasheet / Manual

Summarize:

| 1 | Brief description | 3 |
|---|---------------------------|---|
| 2 | Available models | 3 |
| 3 | Introduction | 3 |
| 4 | Warnings | 3 |
| 5 | Warranty | 4 |
| 6 | Technical data | 4 |
| 7 | Electrical connection | 5 |
| 8 | Dimensions in mm | 5 |
| 9 | Declaration of Conformity | 5 |

1 Brief description

- Stainless steel single point load cell
- Protection class IP67 (according to EN 60529)
- RoHS compliant
- Suitable for platform scales, etc.
- Maximum platform size: 400 x 400 mm
- Accuracy class C3 according to OIML R60
- Optional on request: Accuracy class C4

2 Available models

| Nominal load | Model | |
|--------------|------------|--|
| 30kg | CP 30-3P7 | |
| 50kg | CP 50-3P7 | |
| 75kg | CP 75-3P7 | |
| 100kg | CP 100-3P7 | |
| 150kg | CP 150-3P7 | |

3 Introduction

Please observe the notes in the operating instructions: Read these operating instructions carefully before commissioning, even if you already have experience with SAUTER measuring cells.

After receipt of the measuring cell, it should be checked in advance whether no transport damage has occurred, whether the outer packaging or other parts or even the article itself have been damaged. If any damage is apparent, please notify SAUTER GmbH immediately.

4 Warnings

Observe the national accident prevention regulations.

Incorrect use of the measuring cells can lead to serious injuries, death, property damage and personal injury. Use may only be carried out by trained and experienced personnel.

Never load measuring cells above the Emax range (nominal load, max. capacity). Overloaded measuring cells no longer have the required accuracy. Overloaded or deformed measuring cells must not be used any further and must be replaced immediately.

Never step under suspended loads.

Always install overload or breakage protection on your equipment.

Always observe the permissible static and dynamic loads of the accessories used.

Have measuring cells calibrated at regular intervals.

Load the measuring cell only in its specified load direction. Avoid transverse forces.

Regularly check the measuring cells for deformations and cracks.

For measuring cells with 4-wire connection, the characteristic value changes by shortening or lengthening the supplied cable.

5 Warranty

The warranty is void in the event of:

- Disregarding the specifications in the operating instructions
- Change or open the measuring cell
- Overload
- Mechanical damage
- Damage due to liquids or media
- Natural wear and tear or abrasion
- Improper setup or electrical installation


6 Technical data

| Output sensitivity (FS) | mV/V | 2.0 ± 0.2 |
|--|--------------------|----------------------|
| Maximum capacity (Emax) | kg | 30, 50, 75, 100, 150 |
| Max.number of load cell intervals | nLC | 3000 |
| Ratio of min. LC verification interval | Y = Emax / vmin | 10000 |
| Combined Error | %FS | ≤± 0.0230 |
| Minimum dead load | Of Emax | 0% |
| Safe overload | of Emax | 150 % |
| Ultimate overload | of Emax | 300 % |
| Zero balance | of FS | < ± 1.5 % |
| Excitation, recommended voltage | V | 5 ~ 12 |
| Excitation maximum | V | 18 |
| Input resistance | Ω | 384 ± 4 |
| Output resistance | Ω | $350 \pm 3,5$ |
| Insulation resistance | MΩ | ≥5000 (at 50VDC) |
| Compensated temperature | °C | -10 ~+40 |
| Operating temperature | °C | -35 ~ +65 |
| Storage temperature | °C | -40 ~ + 70 |
| Recommended torque on fixation bolts | Nm | M6: 10 |


7 Electrical connection

Shielded PVC cable, shield not connected to element, cable diameter Ø5mm, standard cable length: 1m

6-wire connection diagram



8 Dimensions in mm



9 Declaration of Conformity

To view the CE declaration, please click on the following link: https://www.kern-sohn.com/shop/de/DOWNLOADS/